



## Overview

Product name	iQ-Flatlight / iQ-Flatlight-VIS-IR ( <b>preliminary</b> )
Principle	A diffuse light panel for illuminating reflective test charts and surfaces based on iQ-LED V2 technology (includes micro-spectrometer) The iQ-LED technology is optimized for the best spectral match and allows CRI values up to 99, depending on illuminant and intensity

## Features

### Diffuse light panel

Light area	620 x 780 mm
------------	--------------

### Illumination

Light source	<p>Different iQ-Flatlight versions:</p> <p>iQ-Flatlight: 10 x iQ-LED V2</p> <p>iQ-Flatlight-VIS-IR: (<b>preliminary</b>) 5x iQ-LED V2 10x iQ-LED IR</p> <p><b>Image Engineering iQ-LED V2 technology:</b> 41 SMD high power LEDs / separated in 20 color channels / Spectral range: 380 – 820 nm / Intensity controlled via 4000 steps per channel and 32 kHz PWM (switchable to 1000 steps with 128 kHz) / An Approx. lifetime of 10,000 hrs. / Typical LED spectra on request</p> <p><b>Image Engineering iQ-LED IR technology:</b> 80 THT LEDs / separated in 10 IR channels and one blue channel / Spectral range: 820 – 1050 nm and one 400nm channel / Intensity controlled via 4000 steps per channel and 32 kHz PWM (switchable to 1000 steps with 128 kHz) / An approx. lifetime of 10,000 hrs. / Typical LED spectra on request</p>
Control functionality without PC	Storage of up to 44 different illuminants and one sequence on the device, default light source, controllable via micro switches on the device without PC



Uniformity on chart plane	Up to 90% (with two iQ-Flatlights in ~1.5 m distance, depending on test setup)								
Illumination stability	+/- 1% when stabilized (2% after switching D illuminants in the first 5 seconds)								
Response time (switch illuminant)	< 50 ms								
Maximum/Minimum illumination level	<p>Single iQ-Flatlight, 400 mm distance (on calibration device):</p> <table border="0"> <tr> <td>iQ-Flatlight</td> <td>25 – 7800 lx for standard D illuminants</td> </tr> <tr> <td>iQ-Flatlight-VIS-IR (<b>preliminary</b>)</td> <td>25 – 3900 lx for standard D illuminants</td> </tr> </table> <p>Two iQ-Flatlights illuminating a test chart (in~1,5 m distance, depending on test setup):</p> <table border="0"> <tr> <td>iQ-Flatlight</td> <td>10 - 2000 lx for standard D illuminants*</td> </tr> <tr> <td>iQ-Flatlight-VIS-IR (<b>preliminary</b>)</td> <td>10 - 1000 lx for standard D illuminants*</td> </tr> </table> <p>* Down to 1lx possible with special settings. Contact our support team for more information.</p>	iQ-Flatlight	25 – 7800 lx for standard D illuminants	iQ-Flatlight-VIS-IR ( <b>preliminary</b> )	25 – 3900 lx for standard D illuminants	iQ-Flatlight	10 - 2000 lx for standard D illuminants*	iQ-Flatlight-VIS-IR ( <b>preliminary</b> )	10 - 1000 lx for standard D illuminants*
iQ-Flatlight	25 – 7800 lx for standard D illuminants								
iQ-Flatlight-VIS-IR ( <b>preliminary</b> )	25 – 3900 lx for standard D illuminants								
iQ-Flatlight	10 - 2000 lx for standard D illuminants*								
iQ-Flatlight-VIS-IR ( <b>preliminary</b> )	10 - 1000 lx for standard D illuminants*								
Dim function	<p>iQ-LED: Software-based by presetting the intensity while the calibration device is in the measurement position or by selecting different pre-stored intensity illuminants directly on the device</p>								
Predefined standard illuminants	<p>D50, D55, D65, D75, A, B, C, E Planckian spectral curve by selected temperature (1900 - 18,000 K)</p>								
Service life	10,000 h (iQ-LED V2)								

## Spectrometer

Construction	Swivel-type calibration device with a spectrometer for changing between measurement position (400 mm distance) and an inoperative state
Spectral range	305 – 1100 nm
Pixel resolution	2048 pixel
FWHM	2.5 nm
Output data	Real-time measurement of spectral trend and radiant power via control software while the calibration device is in the measuring position
Calibration	Yearly calibration required independent of working hours (contact Image Engineering), NIST traceable

## Software

System requirements	<p>PC with Windows 7 operating system (or higher) 2 x USB port</p>
Functions	<ul style="list-style-type: none"> <li>• Auto-generation of standard illuminants or externally measured spectra</li> <li>• Creation or adaptation of spectral trends via 20 LED channels</li> <li>• Save and load function of self-defined spectral arrangements or intensities</li> <li>• Storage of illuminants/sequences on the device</li> <li>• Creation of test sequences</li> <li>• Real-time display of spectral measurement</li> <li>• Real-time calculation of CCT, CRI, curve fit, and illumination level</li> </ul>
API (C++)	iQ-LED API included



## General description hardware

Power supply/consumption	iQ-Flatlight & iQ-Flatlight-VIS-IR ( <b>preliminary</b> ): 100 V – 250 V / 1000 W
Ports	1 x USB for software control 1 x port for the power adaptor 1 x 3.5 mm jack for trigger output
Dimension [W x H x D]	870 x 1530 - 1830 x 710 mm (300 mm height adjustable)
Weight	65 kg
Operating conditions	Optimal: 22 - 26 °C, maximal: 18 - 28 °C
Warm-up time	< 2 min at an optimal ambient temperature
Rolling Cart	Wheels with brakes
Scope of delivery	Pair of iQ-Flatlights, each with a spectrometer (calibration device) and Rolling Cart, 2x power cords, 2 x USB cables, control software, calibration protocol